



Pushing Performance
Since 1945

ix Type A - RJ45 AWG28 CAT6A PVC 7.5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 065 3830 075
Specification	ix Type A - RJ45 AWG28 CAT6A PVC 7.5m
HARTING eCatalogue	https://harting.com/33480653830075

Identification

Category	System cabling
Series	HARTING ix Industrial® RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type A Solder termination
Connector 2	RJ45 Piercing termination
Type of cable	Copper cable (round)

Version

Cable length	7.5 m
Number of cores	8
Core structure	4x 2x AWG 28/7

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +70 °C
----------------------	----------------

Material properties

Material (cable)	PVC
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 61076-3-124
----------------	-----------------

Commercial data

Packaging size	1
Net weight	300 g
Country of origin	Vietnam
European customs tariff number	85444290
GTIN	5713140264199
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600