

ix Type B solder 5x2xAWG26 PVC 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 48 161 6A20 050
Specification	ix Type B solder 5x2xAWG26 PVC 5.0m
HARTING eCatalogue	https://harting.com/33481616A20050

Identification

Category	System cabling
Series	HARTING ix Industrial®
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING ix Industrial® Type B
Connector 2	HARTING ix Industrial® Type B
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	10
Core structure	10x AWG 26
Termination method	Solder termination
Coding	Type B

Technical characteristics

Rated current	1.5 A
Rated voltage	50 V AC 60 V DC
Limiting temperature	-30 ... +80 °C

Material properties

Material (cable)	PVC
------------------	-----



Pushing Performance
Since 1945

Material properties

Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-124
----------------	-----------------

Commercial data

Packaging size	1
Net weight	350 g
Country of origin	Vietnam
European customs tariff number	85444290
GTIN	5713140260115
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600