

Han F+B 17D PFT 0,5mm² f/- st/- PVC 1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 50 440 0339 010
Specification	Han F+B 17D PFT 0,5mm ² f/- st/- PVC 1,0m
HARTING eCatalogue	https://harting.com/33504400339010

Identification

Category	System cabling
Series	Han® F+B
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Female Bulkhead mounted housing
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	17
Core structure	0.5 mm ²
Number of contacts	17
PE contact	Yes

Technical characteristics

Rated current	10 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Limiting temperature	-5 ... +70 °C moved -30 ... +80 °C unmoved
Minimum bending radius	4x Cable diameter (singular bending)

Material properties

Material (cable)	PVC
Colour (cable)	Black Green-yellow

Specifications and approvals

Specifications	EN 50525-2-31 IEC 60227-3 IEC 60228 EN 50363-3 IEC 60227-3 IEC 60332-1-2 Flame retardancy
----------------	--

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140238244
eCl@ss	27060311 Assembled sensor actuator-line
ETIM	EC001855
UNSPSC 24.0	26121604