

## Han 24 B-E CA 2-lever m/- ang/- PVC, 3m



Image is for illustration purposes only. Please refer to product description.

Part number	33 50 B50 0273 030
Specification	Han 24 B-E CA 2-lever m/- ang/- PVC, 3m
HARTING eCatalogue	<a href="https://harting.com/3350B500273030">https://harting.com/3350B500273030</a>

### Identification

Category	System cabling
Series	Han E <sup>®</sup>
Series of hoods/housings	Han <sup>®</sup> B
Element	Cable assemblies
Specification	Pre-assembled on one side

### Version

Cable length	3 m
Size	24 B
Number of contacts	24
PE contact	Yes

Details	<p>Not be coupled or decoupled under electrical load.</p> <p>Assembly and installation must be carried out by a qualified electrician.</p> <p>Protection against electric shock: Protection against indirect contact (fault protection) shall be ensured by suitable measures taken by the user during installation. E. g. by restricted access area (area accessible only to electrically skilled persons and electrically instructed persons).</p>
---------	--

### Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140334403
eCl@ss	27060327 Assembled power cable
UNSPSC 24.0	43211600