

## FO CABLE ASSY-20M-2xHAN3A-2xLC DUPL SM



Image is for illustration purposes only. Please refer to product description.

Part number	33 54 211 0200 001
Specification	FO CABLE ASSY-20M-2xHAN3A-2xLC DUPL SM
HARTING eCatalogue	<a href="https://harting.com/33542110200001">https://harting.com/33542110200001</a>

### Identification

Category	System cabling
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Han® 3 A Metal 2x LC duplex
Connector 2	Han® 3 A Metal 2x LC duplex
Type of cable	FO cable
Description of the cable	Singlemode

### Version

Cable length	20 m
Core structure	9 / 125 µm

### Technical characteristics

Cable diameter	9.5 mm
----------------	--------

### Material properties

RoHS	compliant with exemption
RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140151048
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600