

HD DSUB44p MA DE CABLE ASSY 2m



Image is for illustration purposes only. Please refer to product description.

Part number	33 56 213 2000 025
Specification	HD DSUB44p MA DE CABLE ASSY 2m
HARTING eCatalogue	https://harting.com/33562132000025

Identification

Category	System cabling
Series	D-Sub
Identification	High Density
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	D-Sub High Density With shielded plastic hood and side entry
Connector 2	D-Sub High Density With shielded plastic hood and side entry
Type of cable	Copper cable (round)

Version

Cable length	2 m
Number of cores	44
Core structure	44x AWG 26

Material properties

Material (cable)	PVC
RoHS	compliant with exemption
RoHS exemptions	6(a)-I: Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	380 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140258617
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600