

Hybr.cable Assy,DC,20m,FO+POW-MM-2xHAN3A




Image is for illustration purposes only. Please refer to product description.

Part number	33 57 211 0205 002
Specification	Hybr.cable Assy,DC,20m,FO+POW-MM-2xHAN3A
HARTING eCatalogue	https://harting.com/33572110205002

Identification

Category	System cabling
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Han [®] 3 A Metal LC duplex
Connector 2	Han [®] 3 A Metal LC duplex
Type of cable	Hybrid cable (copper/FO)
Description of the cable	Multimode DC version

Version

Cable length	20 m
Core structure	2x G50 / 125 µm 3x 2.5 mm ²

Technical characteristics

Cable diameter	12.6 mm
----------------	---------

Material properties

Material (cable)	PVC
RoHS	compliant with exemption



Pushing Performance
Since 1945

Material properties

RoHS exemptions	6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight 6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	0.1 g
Country of origin	Germany
European customs tariff number	85447000
GTIN	5713140151741
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600