

HYBRID KABEL 2xFO MM,20M,RING



Image is for illustration purposes only. Please refer to product description.

Part number	33 57 851 0200 002
Specification	HYBRID KABEL 2xFO MM,20M,RING
HARTING eCatalogue	https://harting.com/33578510200002

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Hybrid cable (copper/FO)
Description of the cable	Multimode

Version

Cable length	20 m
Core structure	2x G50 / 125 µm 3x 2.5 mm ²

Technical characteristics

Cable diameter	12.6 mm
Minimum bending radius	10x Cable diameter (repeated bending) 5x Cable diameter (singular bending)

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	1
Net weight	4,400 g
Net weight	217 g/m
Country of origin	Germany
European customs tariff number	85447000
GTIN	5713140274037
eCl@ss	27060501 Hybrid cable
ETIM	EC001579
UNSPSC 24.0	26121639