

FO CA PP2-PP2, 50µ, OM3, PUR, 3m



Image is for illustration purposes only. Please refer to product description.

Part number	33 61 221 0030 002
Specification	FO CA PP2-PP2, 50µ, OM3, PUR, 3m
HARTING eCatalogue	https://harting.com/33612210030002

Identification

Category	System cabling
Series	HARTING PushPull (V4)
Identification	Industrial Fibre Optic
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4)
Connector 2	HARTING PushPull (V4)
Type of cable	FO cable
Description of the cable	Multimode Overmoulded

Version

Cable length	3 m
Core structure	50 / 125 µm

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP68
Cable diameter	6.5 mm

Material properties

Material (hood/housing)	Thermoplastic
Material (cable)	PUR (polyurethane)



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	155 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140260948
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600