

## FO CA PP2-PP2, 62,5µ, OM1, PUR, 20m



Image is for illustration purposes only. Please refer to product description.

Part number	33 61 221 0200 003
Specification	FO CA PP2-PP2, 62,5µ, OM1, PUR, 20m
HARTING eCatalogue	<a href="https://harting.com/33612210200003">https://harting.com/33612210200003</a>

### Identification

Category	System cabling
Series	HARTING PushPull (V4)
Identification	Industrial Fibre Optic
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4)
Connector 2	HARTING PushPull (V4)
Type of cable	FO cable
Description of the cable	Multimode Overmoulded

### Version

Cable length	20 m
Core structure	62.5 / 125 µm

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP68
Cable diameter	6.5 mm

### Material properties

Material (hood/housing)	Thermoplastic
Material (cable)	PUR (polyurethane)



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

## Commercial data

Packaging size	1
Net weight	79 g
Country of origin	Czechia
European customs tariff number	85447000
GTIN	5713140261341
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600