

FO CA PP2-LCdx, 50µ, OM3, PUR, 1m




Image is for illustration purposes only. Please refer to product description.

Part number	33 61 431 0010 002
Specification	FO CA PP2-LCdx, 50µ, OM3, PUR, 1m
HARTING eCatalogue	https://harting.com/33614310010002

Identification

Category	System cabling
Series	HARTING PushPull (V4)
Identification	Industrial Fibre Optic
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING PushPull (V4)
Connector 2	LC duplex
Type of cable	FO cable
Description of the cable	Multimode Overmoulded

Version

Cable length	1 m
Core structure	50 / 125 µm

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP68
Cable diameter	6.5 mm

Material properties

Material (hood/housing)	Thermoplastic
Material (cable)	PUR (polyurethane)



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	1 g
Country of origin	Czechia
European customs tariff number	85444290
GTIN	5713140271173
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600