

D-Sub PushPull 9 pol, MA/FE, PUR,L=0.5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 66 212 0050 195
Specification	D-Sub PushPull 9 pol, MA/FE, PUR,L=0.5m
HARTING eCatalogue	https://harting.com/33662120050195

Identification

Category	System cabling
Series	D-Sub
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	D-Sub Male Straight
Connector 2	D-Sub Female Straight
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Halogen-free Flame retardant

Version

Cable length	0.5 m
Number of cores	9
Core structure	AWG 26/7
Shielding	Shielded
Number of contacts	9
Locking type	PushPull

Technical characteristics

Rated voltage	300 V
Limiting temperature	-40 ... +80 °C



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	6 mm
----------------	------

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	RoHS 2011/65/EU
----------------	-----------------

Commercial data

Packaging size	1
European customs tariff number	85444290
eCl@ss	27060390 Ready-made data cable (unspecified)