

## FORJ, MM 62,5 ST-ST



Image is for illustration purposes only. Please refer to product description.

Part number	33 99 050 0000 005
Specification	FORJ, MM 62,5 ST-ST
HARTING eCatalogue	<a href="https://harting.com/33990500000005">https://harting.com/33990500000005</a>

### Identification

Type of accessory	Fiber optic rotary joint
Description of the accessory	for ST / BFOC connectors fiber type 62.5 / 125 µm

### Technical characteristics

Limiting temperature	-40 ... +75 °C
Insertion loss	≤1 dB typically 1.5 dB max. ≤1 dB change of attenuation @ 30 rotations / min
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

### Commercial data

Packaging size	1
Net weight	23 g
Country of origin	Germany



**Pushing Performance**  
Since 1945

## Commercial data

European customs tariff number	85367000
GTIN	5713140274044
eCl@ss	90909090 Interim classification (unspecified)

---