

Double Frame, Ni plated, plastic cover



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 000 0200
Specification	Double Frame, Ni plated, plastic cover
HARTING eCatalogue	https://harting.com/39500000200

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Frames
Specification	<p>Double Metal version, nickel plated (electrically conductive) Transparent plastic cover</p>

Technical characteristics

Limiting temperature	-10 ... +60 °C
Storage temperature	-25 ... +60 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Smoothed surface
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

Material properties

California Proposition 65 substances	Lead Nickel
--------------------------------------	----------------

Commercial data

Packaging size	1
Net weight	394 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140154780
eCl@ss	27182810 Cover/infill panel/identification strip (electrical cabinet)
ETIM	EC002617
UNSPSC 24.0	39121321