

Plug socket module USA/Japan (NEMA 5-15)




Image is for illustration purposes only. Please refer to product description.

Part number	39 50 001 0004
Specification	Plug socket module USA/Japan (NEMA 5-15)
HARTING eCatalogue	https://harting.com/39500010004

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket
Specification	Finger safe

Version

Termination method	Screw termination
Field of application	USA Japan

Termination data

Supply voltage	125 V AC
Nominal current	15 A
Nominal frequency	60 Hz

Technical characteristics

Conductor cross-section	2.5 mm²
Mounting depth	30 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	80.775 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140154896
eCl@ss	27144042 Plug socket
ETIM	EC000450
UNSPSC 24.0	39121406