

## Plug socket module Euro/USA




Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket
Specification	Finger safe

### Version

Termination method	Screw termination
Field of application	USA Euro

### Termination data

Supply voltage	250 V AC
Nominal current	16 A
Nominal frequency	60 Hz

### Technical characteristics

Conductor cross-section	4 mm²
Mounting depth	30 mm

### Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Commercial data

Packaging size	1
Net weight	78 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140154940
ETIM	EC000450
eCl@ss	27144042 Plug socket