

Plug socket module Denmark



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Socket

Version

Termination method	Spring clamp termination
Field of application	Denmark

Termination data

Supply voltage	250 V AC
Nominal current	13 A
Nominal frequency	50 Hz

Technical characteristics

Conductor cross-section	2.5 mm ²
Mounting depth	20 mm

Material properties

Material (hood/housing)	Thermoplastic
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained

Material properties

REACH ANNEX XIV substances Not contained

REACH SVHC substances Not contained

Commercial data

Packaging size	1
Net weight	74.3 g
Country of origin	Czechia
European customs tariff number	85366990
GTIN	5713140154957
eCl@ss	27144042 Plug socket
ETIM	EC000450
UNSPSC 24.0	39121406