

Plug socket module India



Image is for illustration purposes only. Please refer to product description.

Identification

| | |
|--------------------------|-----------|
| Category | Sockets |
| Series of hoods/housings | Han-Port® |
| Element | Socket |

Version

| | |
|----------------------|-------------------|
| Termination method | Screw termination |
| Field of application | India (IS) |

Termination data

| | |
|-------------------|----------|
| Supply voltage | 240 V AC |
| Nominal current | 5 A |
| Nominal frequency | 50 Hz |

Technical characteristics

| | |
|-------------------------|-------|
| Conductor cross-section | 4 mm² |
| Mounting depth | 20 mm |

Material properties

| | |
|-----------------------------|---------------|
| Material (hood/housing) | Thermoplastic |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |

Material properties

REACH ANNEX XIV substances Not contained

REACH SVHC substances Not contained

Commercial data

| | |
|--------------------------------|----------------------|
| Packaging size | 1 |
| Net weight | 81.8 g |
| Country of origin | India |
| European customs tariff number | 85366990 |
| GTIN | 5713140154964 |
| eCl@ss | 27144042 Plug socket |
| ETIM | EC000450 |
| UNSPSC 24.0 | 39121406 |