

## Data module (USB,RJ45,SUB-D9,f-m)



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Data connectors
Specification	<p>With shielding plate USB female/female gender changer, size A according to specification 3.0 RJ45 female/female gender changer, 8-pin, metal, Cat. 5e D-Sub 1 (9 poles) female/male gender changer</p>

### Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

### Specifications and approvals

UL / CSA	UL 508 NRAQ2.E253944 CSA-C22.2 No. 142 NRAQ8.E253944
----------	---

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140155053
eCl@ss	27182890 Elements for switching cabinet, housing, rack (unspecified)
ETIM	EC002620
UNSPSC 24.0	43223300