

Data module (RJ45;SUB-D9,f-f;SUB-D9,m-m)



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Data connectors
Specification	<p>Without shielding plate RJ45 female/female gender changer, 8-pin, metal, Cat. 5e D-Sub 1 (9 poles) female/female gender changer D-Sub 1 (9 poles) male/male gender changer</p>

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 508 NRAQ2.E253944 CSA-C22.2 No. 142 NRAQ8.E253944
----------	---

Commercial data

Packaging size	1
----------------	---

Commercial data

Net weight	67 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140155121
eCl@ss	27182890 Elements for switching cabinet, housing, rack (unspecified)
ETIM	EC002620
UNSPSC 24.0	43223300