

Inducom Crimp ferrule 9,5 - 10,5mm



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 000 0054
Specification	Inducom Crimp ferrule 9,5 - 10,5mm
HARTING eCatalogue	https://harting.com/61030000054

Identification

Category	Accessories
Series	D-Sub
Type of accessory	Crimp ferrule

Technical characteristics

Ambient temperature	-20 ... +90 °C
Inner diameter	9.5 mm
Outer diameter	10.5 mm

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	100
Net weight	1.667 g
Country of origin	China
European customs tariff number	85389099



Pushing Performance
Since 1945

Commercial data

GTIN	5713140156890
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400