

Inducom Crimp ferrule 14,0 - 15,0mm



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 61 03 000 0061 |
| Specification | Inducom Crimp ferrule 14,0 - 15,0mm |
| HARTING eCatalogue | https://harting.com/61030000061 |

Identification

| | |
|-------------------|---------------|
| Category | Accessories |
| Series | D-Sub |
| Type of accessory | Crimp ferrule |

Technical characteristics

| | |
|---------------------|----------------|
| Ambient temperature | -20 ... +90 °C |
| Inner diameter | 14 mm |
| Outer diameter | 15 mm |

Material properties

| | |
|--------------------------------------|---------------|
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Commercial data

| | |
|--------------------------------|----------|
| Packaging size | 10 |
| Net weight | 2.15 g |
| Country of origin | China |
| European customs tariff number | 85389099 |



Pushing Performance
Since 1945

Commercial data

| | |
|-------------|--|
| GTIN | 5713140229716 |
| eCl@ss | 27440292 Connector component (accessories) |
| ETIM | EC002943 |
| UNSPSC 24.0 | 39121400 |