

Crimp flange for Hood 9-37P 6,0-7,0mm



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 000 0067
Specification	Crimp flange for Hood 9-37P 6,0-7,0mm
HARTING eCatalogue	https://harting.com/61030000067

Identification

Category	Accessories
Series	D-Sub
Type of accessory	Crimp flange
Description of the accessory	D-Sub 1 ... 4

Technical characteristics

Ambient temperature	-20 ... +90 °C
Inner diameter	6 mm
Outer diameter	7 mm

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	6fb545c1-f438-46c2-b07a-8552e7e5a3d7
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead



Pushing Performance
Since 1945

Commercial data

Packaging size	100
Net weight	4.944 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140157019
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400