

InduCom 37p 3T-entry hexscrew M3



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 001 1118
Specification	InduCom 37p 3T-entry hexscrew M3
HARTING eCatalogue	https://harting.com/61030011118

Identification

Category	Hoods / Housings
Series	D-Sub
Identification	InduCom
Type of hood/housing	Shell housing
Description of hood/housing	With internal earth

Version

Size	D-Sub 4
Version	Top/side entry
Number of cable entries	3
Cable entry	3x
Strain relief	An additional InduCom cable clamp or a crimp flange - ferrule combination is available dependant on the use of the cable.
Locking type	Hexagonal screw with captive washer Thread M3
ground connection	With internal grounding block
2 parts	Yes
Separable	Yes
Details	Part number includes two dummy plugs

Technical characteristics

Tightening torque	0.4 Nm ground connection
	0.4 Nm cover screw
	0.4 Nm Locking screw
Limiting temperature	-55 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP30
--	------

Material properties

Material (hood/housing)	Zinc die-cast
Material (screw)	Steel, nickel plated
Length	52 mm
Width	69.5 mm
Height	14.8 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	1
Net weight	99 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140157866
eCl@ss	27440213 D-Sub hood
ETIM	EC001133
UNSPSC 24.0	39121416