

InduCom 15p S40°-entry hexscrew 4-40 w/o



Image is for illustration purposes only. Please refer to product description.

Part number	61 03 001 2014 010
Specification	InduCom 15p S40°-entry hexscrew 4-40 w/o
HARTING eCatalogue	https://harting.com/61030012014010

Identification

Category	Hoods / Housings
Series	D-Sub
Identification	InduCom
Type of hood/housing	Shell housing
Description of hood/housing	Without internal earth

Version

Size	D-Sub 2
Version	40° side entry
Number of cable entries	1
Cable entry	1x
Strain relief	An additional InduCom cable clamp or a crimp flange - ferrule combination is available dependant on the use of the cable.
Locking type	Hexagonal screw with captive washer Thread 4-40 UNC
ground connection	Without internal grounding block
2 parts	Yes
Separable	Yes

Technical characteristics

Tightening torque	0.4 Nm cover screw 0.4 Nm Locking screw
Ambient temperature	-55 ... +125 °C
Degree of protection acc. to IEC 60529	IP30



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Zinc die-cast
Material (screw)	Steel, nickel plated
Length	34.7 mm
Width	39.3 mm
Height	14.8 mm
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Net weight	43.585 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140221949
eCl@ss	27440213 D-Sub hood
ETIM	EC001133
UNSPSC 24.0	39121416