

Powercbl. Han Q4/2 f str 4G1,5 3m



Part number	61 88 780 0103 0
Specification	Powercbl. Han Q4/2 f str 4G1,5 3m
HARTING eCatalogue	https://harting.com/618878001030

Image is for illustration purposes only. Please refer to product description.

Identification

Element	Energy supply
Specification	AC power input
Connector 1	 Han-Compact® Hood Top entry Han® Q 4/2 Female
Type of cable	Copper cable (round)
Features	TC-ER cable

Version

Cable length	3 m
Core structure	4G 1.5 mm ²

Technical characteristics

Type of current	AC
-----------------	----

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead Potassium 1,1,2,2,3,3,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140276086
eCl@ss	27060327 Assembled power cable
ETIM	EC002587
UNSPSC 24.0	43211600