

Ha-MLK4-5M



Image is for illustration purposes only. Please refer to product description.

Part number	72 MN FL4 050
Specification	Ha-MLK4-5M
HARTING eCatalogue	https://harting.com/72MNFL4050

Identification

Category	System cabling
Series	Circular connectors 7/8"
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	7/8" Female Angled
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	4
Core structure	4x AWG 16
Number of contacts	4

Technical characteristics

Limiting temperature	-20 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PVC
Colour (cable)	Black

Specifications and approvals

Approvals	CE
-----------	----



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140236936
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600