

S15_PFT_STR-FM_DC_F_CRT_w/o-contacts



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 4422
Specification	S15_PFT_STR-FM_DC_F_CRT_w/o-contacts
HARTING eCatalogue	https://harting.com/97000004422

Identification

Category	Connectors
Series	Circular connectors Size 15
Element	Panel feed through
Specification	for front mounting

Version

Gender	Female
Shielding	Unshielded
Number of contacts	5
Number of signal contacts	3
Number of power contacts	2
PE contact	Yes
Locking type	Toggle locking
Details	Please order crimp contacts separately.
Pack contents	incl. lock nut

Technical characteristics

Conductor cross-section (mm²)	0.14 ... 2.5 mm²
Conductor cross-section (AWG)	AWG 26 ... AWG 14
Pollution degree	3
Rated current (signal)	4 A
Rated voltage (signal)	48 V AC/DC
Rated impulse voltage (signal)	0.8 kV



Pushing Performance
 Since 1945

Technical characteristics

Pollution degree (signal)	3
Rated current (power)	20 A
Rated voltage (power)	48 V AC/DC
Rated voltage conductor-conductor (Power)	48 V
Rated impulse voltage (power)	0.8 kV
Pollution degree (power)	3
Tightening torque	2 Nm Lock nut
Limiting temperature	-30 ... +90 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 IP67
Isolation group	I (600 ≤ CTI)
Thickness of the panel	1 ... 10 mm

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Polyamide (PA)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61076-2-116 IEC 61984
----------------	------------------------------

Commercial data

Packaging size	25
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440103 Sensor-actuator connector chassis (sensor technology actuator)
UNSPSC 24.0	39121413