







X
(without protection cap)



Loading-Plan

A — black — B
B — orange — A

Y
(without protection cap)



-Temperature range: $-20^{\circ}\text{C} \dots +70^{\circ}\text{C}$
-Protection level: IP 20

For Information Only
-won't be replaced when changed-

Cont No.	Type of cable	Part-No.	Dim. a[mm]
5	Fiber optic cable, 8mm, POF	33 02 211 020 0001	20000
4	Fiber optic cable, 8mm, POF	33 02 211 010 0001	10000
3	Fiber optic cable, 8mm, POF	33 02 211 005 0001	5000
2	Fiber optic cable, 8mm, POF	33 02 211 002 0001	2000
1	Fiber optic cable, 8mm, POF	33 02 211 001 0001	1000

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances		
				Dat.	Name	Maßstab/Scale /	FO cable assembly, 2xIP20-FO-SCRJ,POF				
			Detail.	21.07.11	RO						
			Insp.	21.07.11	RA						
			Stand.								
DRS970A			HARTING Electronics GmbH & Co. KG								
Mod. Dat. Name			D-32339 ESPELKAMP				Sub.				