






X
(without protection hood)

Loading-Plan



- A1 orange 1
- B1 orange 2
- A2 orange 3
- B2 orange 4

-Protection level: IP67/65
-Temperature range: -40°C ...+70°C

9	Fiber optic cable Single Mode, 4 chanel	33 54 111 300 0001	300 m
8	Fiber optic cable Single Mode, 4 chanel	33 54 111 100 0001	100 m
7	Fiber optic cable Single Mode, 4 chanel	33 54 111 060 0001	60 m
6	Fiber optic cable Single Mode, 4 chanel	33 54 111 050 0001	50 m
5	Fiber optic cable Single Mode, 4 chanel	33 54 111 040 0001	40 m
4	Fiber optic cable Single Mode, 4 chanel	33 54 111 020 0001	20 m
3	Fiber optic cable Single Mode, 4 chanel	33 54 111 010 0001	10 m
2	Fiber optic cable Single Mode, 4 chanel	33 54 111 005 0001	5 m
1	Fiber optic cable Single Mode, 4 chanel	33 54 111 001 0001	1 m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------

		Techn. Character.		Nicht tolerierte Maße/Free size tolerances	
		Detail. 23.07.09 MS Insp. 23.07.09 RA Stand.		Fiber optic cable assembly 1xHan 3A 2xLC DUPLEX, metal Single Mode	
DRS531A		HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP		TB 33 54 111 xxx 0001	
Mod.		Dat.		Name	
				Sub.	

For Information only
won't be replaced when changed