

# D-SSK 135 KER - End cover



0205067

<https://www.phoenixcontact.com/us/products/0205067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, insulation material: ceramic



## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0205067             |
| Packing unit                         | 50 pc               |
| Minimum order quantity               | 50 pc               |
| Sales key                            | BE19                |
| Product key                          | BE1Z1X              |
| Catalog page                         | Page 543 (C-1-2019) |
| GTIN                                 | 4017918099022       |
| Weight per piece (including packing) | 37.486 g            |
| Weight per piece (excluding packing) | 37.486 g            |
| Customs tariff number                | 85389099            |
| Country of origin                    | DE                  |

# D-SSK 135 KER - End cover

0205067

<https://www.phoenixcontact.com/us/products/0205067>



## Technical data

### Product properties

|              |           |
|--------------|-----------|
| Product type | End cover |
|--------------|-----------|

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 180 °C                                                         |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (operation)         | 20 % ... 90 %                                                             |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

### Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | cream (RAL 9001) |
| Flammability rating according to UL 94 | V0               |

### Dimensions

|        |       |
|--------|-------|
| Width  | 5 mm  |
| Height | 52 mm |
| Depth  | 63 mm |

# D-SSK 135 KER - End cover



0205067

<https://www.phoenixcontact.com/us/products/0205067>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250301 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000886 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# D-SSK 135 KER - End cover



0205067

<https://www.phoenixcontact.com/us/products/0205067>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)