

TS-RKN - Separating plate



0302216

<https://www.phoenixcontact.com/us/products/0302216>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Separating plate, width: 0.8 mm, color: gray



Commercial data

Item number	0302216
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1Z1X
GTIN	4017918000325
Weight per piece (including packing)	1.48 g
Weight per piece (excluding packing)	1.562 g
Customs tariff number	39269097
Country of origin	DE

TS-RKN - Separating plate

0302216

<https://www.phoenixcontact.com/us/products/0302216>



Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Material specifications

Color	gray (RAL 7042)
Material	PVC
Flammability rating according to UL 94	V0

Dimensions

Width	0.8 mm
-------	--------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 30 °C
Ambient temperature (assembly)	-5 °C ... 60 °C
Ambient temperature (actuation)	-5 °C ... 60 °C
Permissible humidity (storage/transport)	30 % ... 70 %

TS-RKN - Separating plate

0302216

<https://www.phoenixcontact.com/us/products/0302216>



Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TS-RKN - Separating plate



0302216
<https://www.phoenixcontact.com/us/products/0302216>

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com