

# UC-EMLP (60X30) YE CUS - Plastic label

0824563

<https://www.phoenixcontact.com/us/products/0824563>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, can be ordered: by sheet, yellow, labeled according to customer specifications, mounting type: adhesive, text field height: 30 mm, text field width: 60 mm



## Your advantages

- All UC-EMLP ... self-adhesive device markers can also be supplied labeled according to customer requirements

## Commercial data

Item number	0824563
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8147
GTIN	4046356357029
Weight per piece (including packing)	13.67 g
Weight per piece (excluding packing)	13.67 g
Country of origin	PL

# UC-EMLP (60X30) YE CUS - Plastic label

0824563

<https://www.phoenixcontact.com/us/products/0824563>



## Technical data

### Product properties

Product type	Gerätemarker
<b>Marking</b>	
Number of individual labels per row	1
Identification technology	UV LED technology

### Dimensions

Width	60.00 mm
Height	30.00 mm
Depth	1.20 mm
Length	30 mm

### Material specifications

RoHS compliant	yes
Adhesive strength	250 µm
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

### Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish	
Result	Test passed

UV resistance	
Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

# UC-EMLP (60X30) YE CUS - Plastic label

0824563

<https://www.phoenixcontact.com/us/products/0824563>



## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Standards

Standards/regulations	EN 45545-2
-----------------------	------------

## Mounting

Mounting type	adhesive
---------------	----------

# UC-EMLP (60X30) YE CUS - Plastic label

0824563

<https://www.phoenixcontact.com/us/products/0824563>



## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 9.0	EC001288
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UC-EMLP (60X30) YE CUS - Plastic label

0824563

<https://www.phoenixcontact.com/us/products/0824563>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.13 kg CO2e
---------	--------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)