

# US-EMLP (70X15) RD CUS - Plastic label



0830386

<https://www.phoenixcontact.com/us/products/0830386>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Card, can be ordered: by card, red, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 8, text field height: 15 mm, text field width: 70 mm



## Your advantages

- PVC material flammability rating V0 in accordance with UL 94

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0830386                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8149                         |
| GTIN                                 | 4046356715478                  |
| Weight per piece (including packing) | 18.18 g                        |
| Weight per piece (excluding packing) | 18.18 g                        |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | Gerätemarker |
|--------------|--------------|

### Marking

|                                     |                |
|-------------------------------------|----------------|
| Number of individual labels         | 8              |
| Number of individual labels per row | 1              |
| Identification technology           | Thermotransfer |

### Dimensions

|        |          |
|--------|----------|
| Width  | 70.00 mm |
| Height | 14.90 mm |
| Depth  | 0.55 mm  |
| Length | 15 mm    |

### Material specifications

|                                        |                |
|----------------------------------------|----------------|
| RoHS compliant                         | yes            |
| Foil strength                          | 500 µm         |
| Adhesive strength                      | 50 µm          |
| Adhesive                               | Acrylic        |
| Color                                  | red (RAL 3001) |
| Material                               | PVC            |
| Flammability rating according to UL 94 | V0             |
| Components                             | Silicone-free  |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Ambient conditions

|                                                     |                                                                                                         |
|-----------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -30 °C ... 80 °C                                                                                        |
| Recommended storage conditions                      | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                                                   |
| Recommended humidity (storage/transport)            | 50 %                                                                                                    |
| Shelf life                                          | 12 months                                                                                               |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# US-EMLP (70X15) RD CUS - Plastic label



0830386

<https://www.phoenixcontact.com/us/products/0830386>

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# US-EMLP (70X15) RD CUS - Plastic label



0830386

<https://www.phoenixcontact.com/us/products/0830386>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# US-EMLP (70X15) RD CUS - Plastic label



0830386  
<https://www.phoenixcontact.com/us/products/0830386>

## Environmental product compliance

|                                         |                            |
|-----------------------------------------|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)