

EML-HT (20X7)R - High-temperature label



0830645

<https://www.phoenixcontact.com/us/products/0830645>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-temperature label, for thermal transfer printers, resistant for 60 s at up to 300°C

Your advantages

- The EML-HT label is made of an acrylate film that is highly temperature-resistant. It can be used for marking printed circuit boards and in all industrial soldering processes
- Continuous temperature range of -40 °C ... 180 °C, 300 °C for up to 60 seconds
- When combined with the ink ribbon THERMOMARK-RIBBON 110 EML-HT, the marking is highly resistant to high temperatures and chemicals
- The EML-HT ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-HT ... markers in accordance with your requirements

Commercial data

Item number	0830645
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356718394
Weight per piece (including packing)	279.3 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	39269097
Country of origin	DE

EML-HT (20X7)R - High-temperature label



0830645

<https://www.phoenixcontact.com/us/products/0830645>

Technical data

Product properties

Product type	Gerätemarker
Product property	Highly resistant to temperature

Marking

Number of individual labels	4000
Number of individual labels per row	4
Identification technology	Thermotransfer

Dimensions

Width	20.00 mm
Height	7.00 mm
Depth	0.07 mm

Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Acrylate
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
Specification	DIN EN ISO 1518-1:2019-10 (following)

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

EML-HT (20X7)R - High-temperature label



0830645

<https://www.phoenixcontact.com/us/products/0830645>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05 (following)
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 180 °C
Ambient temperature (assembly)	> 4 °C
Short-term temperature	300 °C (1 minute, maximum)
Recommended storage conditions	23 °C / 50 % relative humidity. Storage in poly bags is recommended prior to processing.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	2 years

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

EML-HT (20X7)R - High-temperature label



0830645

<https://www.phoenixcontact.com/us/products/0830645>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0830645>



UL Recognized

Approval ID: MH48542

EML-HT (20X7)R - High-temperature label



0830645

<https://www.phoenixcontact.com/us/products/0830645>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EML-HT (20X7)R - High-temperature label



0830645
<https://www.phoenixcontact.com/us/products/0830645>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com