

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



EVO connector set, B16 series, plastic housing, consisting of sleeve housing, panel mounting base, push-in contact inserts: 1407731, 1407732, 1407647, 1407642, 1407670

## Your advantages

- Lower costs than metal version
- Labeling option using 9 x 20 mm marking label
- Low weight
- Lower risk of condensation

## Commercial data

Item number	1408793
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF63
Product key	AF7AFX
GTIN	4046356834100
Weight per piece (including packing)	472.1 g
Weight per piece (excluding packing)	472.1 g
Customs tariff number	85366990
Country of origin	CN

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

Set consists of

HC-B16-I-PT-F - Contact insert

1407731

<https://www.phoenixcontact.com/us/products/1407731>



Contact insert, number of positions: 16+PE, size: B16, number of connections per position: 1, Socket, Push-in connection, 500 V, 16 A, 0.14 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Power

---

HC-B16-I-PT-M - Contact insert

1407732

<https://www.phoenixcontact.com/us/products/1407732>



Contact insert, number of positions: 16+PE, size: B16, number of connections per position: 1, Pin, Push-in connection, 500 V, 16 A, 0.14 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Power

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

## HC-EVO-B16-BWSC-PLRBK - Housing

1407647

<https://www.phoenixcontact.com/us/products/1407647>



Panel mounting base B16, with single locking latch, material: PA 6.6-FR, protective cover material: PC, height: 30.5 mm, cable gland: none, protective cover: yes, Standard, with flat gasket

## HC-EVO-B16-HHFS-PLBK - Housing

1407642

<https://www.phoenixcontact.com/us/products/1407642>



Sleeve housing B16, for single locking latch, material: PA 6.6-FR, cable outlets: 1, straight/lateral, height: 78 mm, cable gland: none, Standard

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

## HC-B-G-M25-PLRBK - Cable gland

1407670

<https://www.phoenixcontact.com/us/products/1407670>

EVO plastic cable gland with bayonet locking, for housing series B, size M25,  
cable diameter: 9 mm ... 17 mm



# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

## Technical data

### Notes

General	Connectors may be operated only when there is no load/voltage.
---------	--

### Product properties

Product type	Connector set
Housing type	Complete housing
Series	HC-B
Type	B16
Number of positions	16
Connection profile	16+PE
Contact numbering	1 - 16
No. of cable outlets	1
Type of the screw connection	1x M25
Protective cover	yes
Cable outlet	straight
Pg screw connection	none

### Insulation characteristics

Ovvoltage category	III
Degree of pollution	3

### Electrical properties

Rated voltage (III/3)	500 V
Rated surge voltage	6 kV
Rated current	16 A

### Connection data

Connection method	Push-in connection
Connection technology	Push-in connection
Conductor cross section	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (with ferrule) 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (without ferrule)
Connection cross section AWG	26 ... 14 (with ferrule)
Tightening torque	0.5 Nm ... 1.7 Nm (Fixing screws for panel mounting base)
Stripping length	8 mm ... 10 mm

### Dimensions

Dimensional drawing	
---------------------	--

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

Width	53 mm
Height	124 mm
Length	114 mm
Drill hole distance, horizontal	103 mm
Drill hole distance, vertical	32 mm

## Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	86 mm

## Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	V0
Seal material Profile gasket	NBR
Seal material Flat gasket	NBR
Housing material	PA
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PA
Locking latch material	PA

## Cable/line

External cable diameter	9 mm ... 17 mm
-------------------------	----------------

## Mechanical properties

Mechanical data	
Type of the screw connection	1x M25
Locking type	Latch
Insertion/withdrawal cycles	≥ 500

## Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
Enclosure rating (NEMA)	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 100 °C

## Mounting

Assembly note	Coding also using the CP-HC (1686478) coding profiles. HC-B6.. / HC-B10.. for two coding profiles. HC-B16.. / HC-B24.. for four coding profiles.  Connectors may only be operated when there is no load/the power is switched off. Can be used for solid wires and stranded wires with ferrule.
---------------	---

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set




1408793

<https://www.phoenixcontact.com/us/products/1408793>


## Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout


# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

Schematic diagram



Pin assignment, connection side, pin


# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

Schematic diagram




Pin assignment, connection side, socket

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>



Derating diagram

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1408793>

**DNV**

Approval ID: TAE000037S

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

## Classifications

### ECLASS

ECLASS-13.0	27440113
ECLASS-15.0	27440113

### ETIM

ETIM 9.0	EC002636
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-EVO-B16PT-BWSC-HH-M25-PLRBK - Connector set



1408793

<https://www.phoenixcontact.com/us/products/1408793>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)