

SACC-AT04-12PA-RS-IV - Connector housing

1521005

<https://www.phoenixcontact.com/us/products/1521005>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connector housing, Crimp contacts



Commercial data

Item number	1521005
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF72
Product key	AF2IEA
GTIN	4063151984298
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	16.5 g
Country of origin	MX

SACC-AT04-12PA-RS-IV - Connector housing

1521005

<https://www.phoenixcontact.com/us/products/1521005>



Technical data

Notes

General	AT04-12PA-RDBLK
General	Use with Size 16 pin contacts

Product properties

Product type	Contact insert
Series	AT04
Contact numbering	1 - 12
Shielded	no

Electrical properties

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
Insulation resistance	1000 MΩ (at 25 °C)
Nominal voltage U _N	50 V AC/DC (IEC rating)
Nominal current I _N	13 A (MAX)

Connection data

Connection method	Crimp contacts
-------------------	----------------

Dimensions

Dimensional drawing	
Width	40.5 mm
Height	22.2 mm
Length	50.6 mm

Material specifications

Seal material Profile gasket	Silicon
Seal material Cable seal	Silicon
Housing material	PA-GF

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 100

Characteristics

Specific dielectric strength	1500 V AC (Less than 2 mA current leakage)
------------------------------	--------------------------------------------

Environmental and real-life conditions

SACC-AT04-12PA-RS-IV - Connector housing

1521005

<https://www.phoenixcontact.com/us/products/1521005>



Ambient conditions

Degree of protection	IP68 (in mated condition) IP69K (in mated condition)
Ambient temperature (operation)	-55 °C ... 125 °C

SACC-AT04-12PA-RS-IV - Connector housing


1521005

<https://www.phoenixcontact.com/us/products/1521005>




Drawings

Dimensional drawing



AT04-12PA top view and side view

Schematic diagram



AT04-12PA pin assignment

SACC-AT04-12PA-RS-IV - Connector housing

1521005

<https://www.phoenixcontact.com/us/products/1521005>



Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

SACC-AT04-12PA-RS-IV - Connector housing

1521005

<https://www.phoenixcontact.com/us/products/1521005>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com