

VS-25-ST-DSUB-EG - D-SUB connector

1689899

<https://www.phoenixcontact.com/us/products/1689899>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact insert, shell size 3, with 25 signal contacts, type of contact pin, with solder cup, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-25...



Your advantages

- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly
- D-SUB 25 connection

Commercial data

Item number	1689899
Packing unit	50 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4017918914295
Weight per piece (including packing)	13.142 g
Weight per piece (excluding packing)	10.76 g
Customs tariff number	85369010
Country of origin	DE

VS-25-ST-DSUB-EG - D-SUB connector

1689899

<https://www.phoenixcontact.com/us/products/1689899>



Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	25
Connection profile	D-SUB 25
Shielded	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

Connection data

Connection method	Solder cup
-------------------	------------

Dimensions

Width	14.3 mm
Height	53.4 mm
Length	12.93 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel
Contact carrier material	PBT-GF

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 50
Insertion force per signal contact	≤ 3.40 N

Environmental and real-life conditions

Ambient conditions	
--------------------	--

VS-25-ST-DSUB-EG - D-SUB connector

1689899

<https://www.phoenixcontact.com/us/products/1689899>



Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C

Mounting

Mounting type	Hole
---------------	------

VS-25-ST-DSUB-EG - D-SUB connector


1689899

<https://www.phoenixcontact.com/us/products/1689899>



Drawings

Schematic diagram



VS-25-ST-DSUB-EG - D-SUB connector

1689899

<https://www.phoenixcontact.com/us/products/1689899>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1689899>



UL Recognized

Approval ID: E118976

VS-25-ST-DSUB-EG - D-SUB connector

1689899

<https://www.phoenixcontact.com/us/products/1689899>



Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-25-ST-DSUB-EG - D-SUB connector

1689899

<https://www.phoenixcontact.com/us/products/1689899>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a11d54ae-67c6-4245-81ec-199e80dd86d4

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com