

PLD M-ME MC/D40 - Mounting holder

2702492

<https://www.phoenixcontact.com/us/products/2702492>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting holder, for machine lights PLD M 260 .../D40, Swiveling range $\pm 20^\circ$



Commercial data

Item number	2702492
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL22Z
GTIN	4055626217017
Weight per piece (including packing)	48.6 g
Weight per piece (excluding packing)	48.6 g
Customs tariff number	94059900
Country of origin	DE

PLD M-ME MC/D40 - Mounting holder

2702492

<https://www.phoenixcontact.com/us/products/2702492>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Assembly element
Special properties	for machine lights PLD M 260 .../D40
	Swiveling range $\pm 20^\circ$

Material specifications

Color	gray
Material ()	Aluminum (AlMgSi0,5)

Mounting

Mounting type	Screw mounting
Mounting type	PLD machine light

PLD M-ME MC/D40 - Mounting holder

2702492

<https://www.phoenixcontact.com/us/products/2702492>



Classifications

ECLASS

ECLASS-13.0	27111126
ECLASS-15.0	27111126

ETIM

ETIM 9.0	EC002557
----------	----------

UNSPSC

UNSPSC 21.0	39111500
-------------	----------

PLD M-ME MC/D40 - Mounting holder

2702492

<https://www.phoenixcontact.com/us/products/2702492>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	85b1d9b1-12b5-4bde-8668-0098dec335ae

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com