

FLT-ISG-PL-14 - Fixing plate

2905586

<https://www.phoenixcontact.com/us/products/2905586>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plate for fixing the FLT-ISG-100-EX isolating spark gap to a flange, drill hole diameter of 14 mm.



Commercial data

Item number	2905586
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL01
Product key	CL1134
GTIN	4055626002415
Weight per piece (including packing)	114.8 g
Weight per piece (excluding packing)	108.7 g
Customs tariff number	73269098
Country of origin	DE

FLT-ISG-PL-14 - Fixing plate

2905586

<https://www.phoenixcontact.com/us/products/2905586>



Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Material specifications

Color	zinc color
	gray (RAL 7042)
Material	St/tZn

Mounting

Mounting type	Screw mounting
---------------	----------------

FLT-ISG-PL-14 - Fixing plate


2905586

<https://www.phoenixcontact.com/us/products/2905586>



Drawings

Dimensional drawing



FLT-ISG-PL-14 - Fixing plate



2905586

<https://www.phoenixcontact.com/us/products/2905586>

Classifications

ECLASS

ECLASS-13.0	27170692
ECLASS-15.0	27170692

ETIM

ETIM 9.0	EC000490
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

FLT-ISG-PL-14 - Fixing plate

2905586

<https://www.phoenixcontact.com/us/products/2905586>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.523 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com