

# VMT-GALGENANSCHLUSS STEHEND - Holder



2913399

<https://www.phoenixcontact.com/us/products/2913399>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Accessories, bracket connection adapter for a monitor/IPC in IP65 housing



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2913399                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | DR12                           |
| Product key                          | DRBBAZ                         |
| GTIN                                 | 4046356341486                  |
| Weight per piece (including packing) | 11.111 g                       |
| Weight per piece (excluding packing) | 11.111 g                       |
| Customs tariff number                | 73269098                       |
| Country of origin                    | DE                             |

# VMT-GALGENANSCHLUSS STEHEND - Holder



2913399

<https://www.phoenixcontact.com/us/products/2913399>

## Technical data

### Product properties

|              |                   |
|--------------|-------------------|
| Product type | Mounting material |
|--------------|-------------------|

Environmental product compliance

EU RoHS

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
|-----------------------------------------|-------------------------------------------------------------------------------------|

EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|