

# UM 25-PROFIL 100CM - Profile

2915795

<https://www.phoenixcontact.com/us/products/2915795>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, DIN rail mounting, Basic profile, profile width (internal): 22 mm, profile width (external): 24.8 mm, length: 1000 mm, Note: required profile length = PCB length - 3 mm

## Your advantages

- Flexible size and shape
- Fast mounting
- Inexpensive as a result of reducing the number of separate housing parts

## Commercial data

Item number	2915795
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDBA
GTIN	4046356178686
Weight per piece (including packing)	200 g
Weight per piece (excluding packing)	200 g
Customs tariff number	39162000
Country of origin	DE

# UM 25-PROFIL 100CM - Profile

2915795

<https://www.phoenixcontact.com/us/products/2915795>



## Technical data

### Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM25
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Length	1 m

#### External dimensions

Profile width (external)	24.8 mm
--------------------------	---------

#### Internal dimensions

Profile width (internal)	22 mm
--------------------------	-------

### Material specifications

Color (Housing)	green (RAL 6021)
Material	PVC
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# UM 25-PROFIL 100CM - Profile


2915795

<https://www.phoenixcontact.com/us/products/2915795>



## Drawings

Dimensional drawing



# UM 25-PROFIL 100CM - Profile

2915795

<https://www.phoenixcontact.com/us/products/2915795>



## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM 25-PROFIL 100CM - Profile

2915795

<https://www.phoenixcontact.com/us/products/2915795>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)