

# ESB 2-FK - Insertion bridge

3131138

<https://www.phoenixcontact.com/us/products/3131138>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 6.15 mm, number of positions: 2, length: 10 mm, color: gray



## Commercial data

Item number	3131138
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918093006
Weight per piece (including packing)	1.49 g
Weight per piece (excluding packing)	1.38 g
Customs tariff number	85366990
Country of origin	PL

# ESB 2-FK - Insertion bridge

3131138

<https://www.phoenixcontact.com/us/products/3131138>



## Technical data

### Product properties

Product type	Insertion bridge
Number of positions	2
Pitch	6.15 mm

### Dimensions

Width	3 mm
Height	24 mm
Length	10.2 mm
Pitch	6.15 mm

### Material specifications

Color	gray
Material	PA 66 V2
Flammability rating according to UL 94	PA66 V2

# ESB 2-FK - Insertion bridge

3131138

<https://www.phoenixcontact.com/us/products/3131138>



## Classifications

### ETIM

ETIM 8.0

EC000489

### UNSPSC

UNSPSC 21.0

39121400

# ESB 2-FK - Insertion bridge

3131138

<https://www.phoenixcontact.com/us/products/3131138>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)