3ft (0.9m) USB-C Charging Cable 2-Pack, USB C Cable, USB 2.0 Type-C Laptop Charger Cord, 60W 3A Power Delivery, TPE Jacket, USB-C Data Transfer Cable, M/M

Product ID: USB2CC3FBKE2PK



Ensure that a spare cable is readily available, with this USB-C Cable 2-pack. Seamlessly charge a USB Type-C mobile device or transfer files to a USB-C host computer. The USB-C charger cord facilitates up to 60W Power Delivery and 3A output for fast charging. It supports USB 2.0 (480Mbps) transfer rates and is suitable for general use.

Designed for frequent charging, the USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 3-foot (0.9-meter) USB Type-C cable is the ideal length for desk workstations, commuters, in-car use or to reduce clutter when syncing with a USB-C laptop.

With up to 3A of output, the USB-C Charger Cord supports up to 60W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Certifications, Reports and Compatibility

Applications

• Charge and sync a USB-C device from an available USB-C port on a laptop or desktop computer

• Charge your USB-C devices using a USB-C wall charger, car charger or power bank

Features

• PRACTICAL 2 PACK: Enable a spare USB-C connection with this USB C Cable 2-pack; Delivers 60W/3A output for fast charging portable Type-C devices; Connect a laptop or tablet to a USB-C wall charger or power bank

• QUALITY CONSTRUCTION: Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 8mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection

• APPLICATIONS: Use this 2-Pack to enable an additional connection without swapping cables; Universal compatibility w/USB-C PD-enabled devices; Supports USB 2.0 for file transfer and device synchronization when connected to a USB-C host or external storage

• PERFORMANCE: 3-foot (0.9-meter); 60W/3A Power Delivery 2.0; USB 480Mbps; Color: Black; O.D.: 0.14in (3.5mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this USB-C charging cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This USB Type-C cable is available in other lengths

General		
	UPC	065030912112
	Package Quantity	2
	Warranty	Lifetime
Special Notes / Requirements		
	Special Notes	Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode)
Power		
	Power Source	USB-Powered
	Power Delivery	60W
	Input Current	3A
Physical & Environmental		
	Color	Black
	Material	Polyamide Resin
	Connector Style	Straight
	Wire Gauge	24/30 AWG

	Cable Length	36.0 in [91.4 cm]
	Cable OD	0.1 in [3.5 mm]
	Product Length	36.0 in [91.5 cm]
	Product Width	0.5 in [12.2 mm]
	Product Height	0.2 in [6.3 mm]
	Weight of Product	0.7 oz [20.0 g]
	Operating Temperature	-10 to 60 (14&degF to 140&degF)
	Storage Temperature	-20 to 70 (-4&degF to 158&degF)
	Humidity	5%~85%
Performance		
	Insertion Rating	Rated over 10,000 insertion cycles
	MTBF	Rated over 10,000 insertion cycles
Hardware		
	Active or Passive Adapter	Passive
	Connector Plating	Nickel
	Cable Jacket Material	TPE (Thermoplastic Elastomer)
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Packaging & In-the-Box		
	Included in Package	2 - USB-C Cable - M/M
	Package Width	5.6 in [14.1 cm]
	Package Depth	5.0 in [12.7 cm]
	Package Height	1.2 in [30 mm]
	Shipping (Package) Weight	1.6 oz [46 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	USB-C (480Mbps, 2.5W)

Connector 2 (Quantity)	1
Connector 2	USB-C (480Mbps, 2.5W)

***Product appearance and specifications are subject to change without notice.**