5-Pack 3ft (91cm) White USB-C Charging Cable, 60W (3A) PD, Dual-Layer Braided Nylon/TPE Jacket, Rugged USB C Charging Cord, USB 2.0 Laptop Charger Cable

Product ID: USB2CC3FNCBRWH5PK



This 5-pack of USB-C cables is a convenient solution for supporting multiple installations. Connect a charger or hub to a USB PD-enabled device, delivering up to 60W Power Delivery and 3A output for fast charging. Clear markings on each connector eliminate confusion, helping you identify the right cable instantly. No more guesswork with lookalike or unmarked USB-C cords.

Rugged and Flexible

The USB-C Charging Cable features a TPE inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 10,000 insertion cycles.

Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 3-foot (91cm) USB Type-C cable is the ideal length for mobile workstations or in-car use.

Power a Laptop

With up to 3A of output, the USB-C Charger Cord supports up to 60W of Power Delivery to charge a USB-C laptop or fast-charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Certifications, Reports and Compatibility

Applications

Features

• PRACTICAL 5 PACK: High quality USB-C cable delivers up to 60W/3A Power Delivery for fast charging USB-C laptops and mobile devices; Convenient 5-pack facilitates multiple device connections; Performance markings on connectors for easy identification

• QUALITY CONSTRUCTION: Dual-layer jacket incorporates a TPE inner layer for optimal flexibility and a braided nylon exterior for rugged use; Designed to withstand frequent -/+90 bends; Nickel-plated connectors rated beyond 10,000 insertions

• APPLICATIONS: Use this 5-Pack to enable additional connections without swapping cables; Universal compatibility with USB-C PD-enabled devices; Supports USB 2.0 for general file transfer and device syncing with a USB-C host computer or external storage

• PERFORMANCE: 3-foot (91cm); 60W/3A Power Delivery 2.0; USB 480Mbps; Color: White; 23/28AWG; O.D.: 0.18in (4.5mm); Dual-layer TPE Jacket with Braided Nylon; NOTE: USB-C video (DP Alt Mode) is not supported

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this USB-C charging cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This USB Type-C cable is available in other lengths

General		
	UPC	065030916240
	Package Quantity	5
	Warranty	Lifetime
Power		
	Power Delivery	60W
	Input Current	3A
Physical & Environmental		
	Color	White
	Material	PE
	Connector Style	Straight
	Wire Gauge	23/28 AWG
	Cable Length	36.0 in [91.4 cm]
	Cable OD	0.2 in [4.5 mm]

	Product Length	36.5 in [92.8 cm]
	Product Width	0.4 in [11.2 mm]
	Product Height	0.3 in [6.5 mm]
	Weight of Product	1.2 oz [34 g]
	Operating Temperature	-20 to 40 (-4&degF to 104&degF)
	Storage Temperature	-20 to 70 (-4&degF to 158&degF)
	Humidity	30%~70%
Performance		
	Insertion Rating	Rated beyond 10,000 insertions
	MTBF	Rated beyond 10,000 insertions
Hardware		
	Connector Plating	Nickel
	Cable Jacket Material	TPE (Thermoplastic Elastomer) with Braided Nylon
Packaging & In-the-Box		
	Included in Package	5 - Braided USB-C Cable - White
	Package Width	5.1 in [13 cm]
	Package Depth	5.5 in [14 cm]
	Package Height	2.2 in [55 mm]
	Shipping (Package) Weight	7.4 oz [210.5 g]
Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	USB-C (480Mbps, 2.5W)
	Connector 2 (Quantity)	1
	Connector 2	USB-C (480Mbps, 2.5W)

Product appearance and specifications are subject to change without notice.