

BMKL 27X12,5 SR - Label sheet, DIN A4

0803676

<https://www.phoenixcontact.com/us/products/0803676>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, Sheet, silver-colored, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, Number of individual labels: 126, text field height: 12.5 mm, text field width: 27 mm



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"
- The unperforated SK-U... sheets are available for custom label designs

Commercial data

Item number	0803676
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG13
Product key	BG2414
GTIN	4017918007638
Weight per piece (including packing)	14.26 g
Weight per piece (excluding packing)	14.26 g
Customs tariff number	39199080
Country of origin	FR

BMKL 27X12,5 SR - Label sheet, DIN A4

0803676

<https://www.phoenixcontact.com/us/products/0803676>



Technical data

Product properties

Product type	Gerätemarker
Marking	
Number of individual labels	126
Number of individual labels per row	6
Identification technology	Office laser printing

Mounting

Mounting type	adhesive
Material specifications	

Material specifications

Foil strength	46 µm
Adhesive strength	29 µm
Adhesive	Acrylic
Color	silver-colored
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 120 °C (min.)
Ambient temperature (assembly)	> 5 °C
Recommended storage conditions	23 °C / 50 % relative humidity
Recommended ambient temperature (storage/transport)	20 °C ... 25 °C
Recommended humidity (storage/transport)	40 % ... 50 %
Shelf life	2 years

Dimensions

Width	12.50 mm
Height	27.00 mm
Depth	0.09 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Notes

General	Print image may vary depending on laser printer
---------	---

BMKL 27X12,5 SR - Label sheet, DIN A4


0803676

<https://www.phoenixcontact.com/us/products/0803676>



Drawings

Dimensional drawing



BMKL 27X12,5 SR - Label sheet, DIN A4

0803676

<https://www.phoenixcontact.com/us/products/0803676>



Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BMKL 27X12,5 SR - Label sheet, DIN A4

0803676

<https://www.phoenixcontact.com/us/products/0803676>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com