

# WT-BASE HF 5 - Cable binder base



3240702

<https://www.phoenixcontact.com/us/products/3240702>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binder base, for cable binders up to 5 mm wide, screwable, 3.5 mm fixing hole, 2-sided cable binder feed-through

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240702       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BE07          |
| Product key                          | BE713Z        |
| GTIN                                 | 4046356703895 |
| Weight per piece (including packing) | 0.6 g         |
| Weight per piece (excluding packing) | 0.6 g         |
| Customs tariff number                | 39269097      |
| Country of origin                    | TW            |

# WT-BASE HF 5 - Cable binder base



3240702

<https://www.phoenixcontact.com/us/products/3240702>

## Technical data

### Product properties

|                      |           |
|----------------------|-----------|
| Product type         | Cable tie |
| Tensile strength GRP | 220 N     |

### Dimensions

|                        |        |
|------------------------|--------|
| Width                  | 9.5 mm |
| Height                 | 7 mm   |
| Length                 | 15 mm  |
| Hole diameter          | 3.5 mm |
| Diameter mounting hole | 3.5 mm |

### Internal dimensions

|              |      |
|--------------|------|
| Width_inside | 5 mm |
|--------------|------|

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | transparent                    |
| Material                               | PA 6.6                         |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Cable/line

|                  |       |
|------------------|-------|
| Tensile strength | 220 N |
|------------------|-------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (assembly)  | -10 °C ... 60 °C |

### Mounting

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

# WT-BASE HF 5 - Cable binder base



3240702

<https://www.phoenixcontact.com/us/products/3240702>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 23159090 |
| ECLASS-15.0 | 23159090 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC011571 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-BASE HF 5 - Cable binder base



3240702

<https://www.phoenixcontact.com/us/products/3240702>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)