

EMLP (27X27)R SR CUS - Label



0827469

<https://www.phoenixcontact.com/us/products/0827469>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, can be ordered: by line, silver, labeled according to customer specifications, mounting type: adhesive, text field height: 27 mm, text field width: 27 mm

Your advantages

- The EMLP ... self-adhesive markers are particularly suited to marking electrical components, devices, and buttons
- The markers meet the same standards as the engraved labels, they provide high-quality visuals
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements

Commercial data

Item number	0827469
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4046356430852
Weight per piece (including packing)	1.31 g
Weight per piece (excluding packing)	1.09 g
Country of origin	PL

EMLP (27X27)R SR CUS - Label



0827469

<https://www.phoenixcontact.com/us/products/0827469>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels per row	2
-------------------------------------	---

Dimensions

Width	26.80 mm
Height	26.80 mm
Depth	0.55 mm
Length	27 mm

Material specifications

RoHS compliant	yes
Foil strength	175 µm
Adhesive strength	400 µm
Adhesive	Acrylic
Color	silver
Material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Ambient temperature (storage/transport)	4 °C ... 38 °C
Ambient temperature (assembly)	> 18 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

EMLP (27X27)R SR CUS - Label



0827469

<https://www.phoenixcontact.com/us/products/0827469>

Mounting

Mounting type	adhesive
---------------	----------

EMLP (27X27)R SR CUS - Label



0827469

<https://www.phoenixcontact.com/us/products/0827469>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMLP (27X27)R SR CUS - Label



0827469

<https://www.phoenixcontact.com/us/products/0827469>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com