

# CF 500/DIE RCT 10-1 - Crimp insert



1212245

<https://www.phoenixcontact.com/us/products/1212245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for tubular cable lugs 4 mm<sup>2</sup> ... 10 mm<sup>2</sup>, **4 mm<sup>2</sup>:** outer Ø 5 mm, inner Ø 3 mm, **6 mm<sup>2</sup>:** outer Ø 6.5 mm, inner Ø 3.5 mm, **10 mm<sup>2</sup>:** outer Ø 7 mm, inner Ø 4.5 mm

## Product description

Outside/inside Ø (mm): **4 mm<sup>2</sup>:** 5/3; **6 mm<sup>2</sup>:** 6.5/3.8; **10 mm<sup>2</sup>:** 7/4.5

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212245       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH32          |
| Product key                          | BH323Z        |
| GTIN                                 | 4046356450034 |
| Weight per piece (including packing) | 64.9 g        |
| Weight per piece (excluding packing) | 64.9 g        |
| Customs tariff number                | 84799070      |
| Country of origin                    | DE            |

# CF 500/DIE RCT 10-1 - Crimp insert

1212245

<https://www.phoenixcontact.com/us/products/1212245>



## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | Die          |
| Compression  | Indent crimp |

### Connection data

|                             |  |
|-----------------------------|--|
| Conductor connection        |  |
| Cross section range, metric | 4 mm <sup>2</sup> ... 10 mm <sup>2</sup> |

### Material specifications

|       |        |
|-------|--------|
| Color | silver |
|-------|--------|

### Cable/line

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 2.4 mm ... 3.7 mm |
|-------------------------|-------------------|

# CF 500/DIE RCT 10-1 - Crimp insert

1212245

<https://www.phoenixcontact.com/us/products/1212245>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212245>



**EAC**

Approval ID: RU C-DE.AI30.B.01549

# CF 500/DIE RCT 10-1 - Crimp insert

1212245

<https://www.phoenixcontact.com/us/products/1212245>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 17130192 |
| ECLASS-15.0 | 17130192 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002778 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CF 500/DIE RCT 10-1 - Crimp insert

1212245

<https://www.phoenixcontact.com/us/products/1212245>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

[info@phoenixcon.com](mailto:info@phoenixcon.com)