

FPM 15.6 69K - Monitor



1261660

<https://www.phoenixcontact.com/us/products/1261660>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hygiene monitor with 39.6 cm/15.6" display (capacitive multi-touchscreen), 1920 x 1080 pixels (Full HD) in all-around closed stainless-steel housing without screws or sharp edges.

Your advantages

- Robust and high-performance under extreme conditions
- Stable and resistant with a closed stainless-steel housing
- Hygienic design with passive cooling
- Easy mounting with boom adapter or VESA adapter
- Capacitive multi-touch display for convenient multi-finger operation with gloves

Commercial data

Item number	1261660
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBBAD
GTIN	4063151371562
Weight per piece (including packing)	6 g
Weight per piece (excluding packing)	4.8 g
Customs tariff number	85285210
Country of origin	DE

FPM 15.6 69K - Monitor

1261660

<https://www.phoenixcontact.com/us/products/1261660>



Technical data

Notes

Order information:	Please note that an adapter listed under "Accessories" is required to operate the device.
--------------------	---

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Monitor
Computer data	
Processor	without processor
Operating system	without operating system
RAM	without RAM
Data storage system	without data storage
Cooling	passive
Slots	without slots
Extras	without

Display

Display type	39.6 cm / 15.6"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	400 cd/m ²
MTBF	50000 h
Color spectrum	16.2 million colors
Reading angle left	90.00 °
Reading angle right	90.00 °
Reading angle top	90.00 °
Reading angle bottom	90.00 °

System properties

User software	without user software
---------------	-----------------------

Electrical properties

Supply	
Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC

Interfaces

Interfaces	1x USB 2.0
Optional interfaces	Without optional interface

FPM 15.6 69K - Monitor

1261660

<https://www.phoenixcontact.com/us/products/1261660>



Monitor output	1x DisplayPort
Network	without network
Bus system	without bus system

Dimensions

External dimensions

Width / Height / Depth	372 mm / 239 mm / 31 mm
------------------------	-------------------------

Material specifications

Material front plate	Glass (3 mm), hardened and non-reflective
Housing material	Stainless steel, fully enclosed

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP69K
Ambient temperature (operation)	0 °C ... 45 °C
Permissible humidity (operation)	10 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 85 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Mounting

Mounting type	VESA holder (via adapter)
	Tube mounting (via adapter)
Holder system	VESA MIS-D 100 C

FPM 15.6 69K - Monitor

1261660

<https://www.phoenixcontact.com/us/products/1261660>



Classifications

ECLASS

ECLASS-13.0	19200201
ECLASS-15.0	19200201

ETIM

ETIM 9.0	EC001428
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

FPM 15.6 69K - Monitor

1261660

<https://www.phoenixcontact.com/us/products/1261660>



Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com